



TUFLUOR® PTFE CHEM FULL CONDUCTIVE

© 2015 THE CHEMOURS COMPANY. CHEMOURS™ AND TEFLON™ ARE TRADEMARKS OF THE CHEMOURS COMPANY. TEFLON™ IS USED UNDER LICENSE BY TUBIGOMMA DEREGIBUS SRL SOCIETÀ UNIPERSONALE



SMOOTH, BLACK, CONDUCTIVE, CLOTH FINISH EPDM
STAINLESS STEEL WIRE HELICES
SYNTHETIC PLIES
SMOOTH, BLACK, CONDUCTIVE TEFLON™ PTFE

Suction and delivery hose designed according to EN 12115 standards for chemicals and solvents, except for chlorine trifluoride, chlorine and fluorine gas, oxygen difluoride, phosgene and molten alkalis (for ex. sodium). Designed for the chemical industry, foodstuff, pharmaceutical and cosmetic industry, where a flexible connection is required. The hose is produced with high quality elastomers, with excellent chemical and mechanical properties. Not intended for use as an implant material. Not suitable for blood or human fluids. Tested and certified hose by BUREAU VERITAS for use in Atex area (Ex-Zone).

DESCRIPTION

Tube

TEFLON™ PTFE, black, conductive, smooth, phthalates free, tested in compliance with 1907/2006/CE (REACH). TEFLON™ PTFE is a polymer with excellent resistance to high temperature, mechanical stress and to oxidation. It complies with FDA 21 CFR 177.1550 standards, USP XXXII class VI, ISO 10993 Sections 5,10,11:2009, EUROPEAN REGLEMENT 1935/2004/CE AND 10/2011/CE

Reinforcement

synthetic plies, stainless steel wire helices, a/s wire to discharge static electricity

Cover

smooth, EPDM, black, conductive, cloth finish. Abrasion, ageing and ozone resistant

Marking

red/white/blue tape

TUDERTECNICA TUFLUOR® PTFE CHEM FULL CONDUCTIVE

embossed according to norm EN 12115

TUDERTECNICA PTFE EN12115:2011 DN SD PN 16 BAR Ω/T Q/Y

TECHNICAL CHARACTERISTICS

Temperature range : -40°C / +150°C (-40°F / +302°F)

The operating temperature of the hose is directly dependent upon the specific fluid been conveyed and the length of time the fluid is in contact with the hose.

Electrical properties : type Ω/T according to norm EN 12115 (R<10⁶ Ω, R<10⁹ Ω through the hose wall)

Norm : EN12115 - TRbF 131/2



Sterilization

refer to guidelines for cleaning and sanitizing on Tudertecnica website

Inside diameter		Outside diameter		Length		Vacuum		Working pressure		Burst pressure		Appr. weight		Bending radius	
[mm]	[in]	[mm]	[in]	[mt]	[ft]	[bar]	[psi]	[bar]	[psi]	[bar]	[psi]	[kg/mt]	[lbs/ft]	[mm]	[in]
13	0,50	25	1,00	40	130	0,9	13	16	250	64	1000	0,54	0,36	90	3,54
19	0,75	31	1,22	40	130	0,9	13	16	250	64	1000	0,70	0,47	130	5,12
25	1,00	37	1,46	40	130	0,9	13	16	250	64	1000	0,86	0,58	170	6,69
32	1,25	44	1,73	40	130	0,9	13	16	250	64	1000	1,18	0,79	215	8,46
38	1,50	51	2,00	40	130	0,9	13	16	250	64	1000	1,43	0,96	255	10,04
50	1,97	66	2,60	40	130	0,9	13	16	250	64	1000	2,08	1,39	330	12,99
63,5	2,50	79,5	3,13	20	65	0,9	13	16	250	64	1000	2,96	1,98	430	16,93
75	2,95	91	3,58	20	65	0,9	13	16	250	64	1000	3,43	2,30	510	20,08
100	3,94	116	4,57	20	65	0,9	13	16	250	64	1000	4,60	3,08	675	26,57

Data refer to ambient temperature (20°C).

We reserve the right to supply in random lengths shorter than 40mt or 20mt.